



CGB239 - CGB Series - Unarmored Cable Connector 3/4" NPT Zinc Plated Steel

By Killark
Catalog # [CGB239](#)



The CGB connector is for use all unarmored cable and flexible cords. This connector features a removable "top-hat" sleeve seal and is designed to cover a broader range of cable diameters for carrying less stocking SKU's. Superior ingress protection with Type 3,3R,4,4X,12 ratings. Designed and certified for NEC and CEC applications.

Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from 1/2" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

General

Catalog Number	CGB239
Finish Name	Natural
Ingress Protection	Type 3R, 4, 4X, 12
Material	Steel
Operating Temperature	- 40C to +80 °C
Series	CGB
UPC	783936184555

Dimensions

Hub Size 3/4"

Conductor Related

Cable Range .393 - .709 in

Product Assets

- [3D Models - CGB239 3D Model](#)
- [3D Models - CGB239 3D Model](#)
- [Brochures - Killark CGB Gland Flyer - English](#)
- [Brochures - CGB Series A Revolutionary Cable Connector for Industrial and Hazardous Applications](#)
- [Brochures - Killark CGB Gland Flyer - French](#)
- [Catalog Page - CGB Glands Catalog](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - KIL_CGB UL Certificate_UL](#)
- [Engineering Drawing - CGB239 Engineering Drawing](#)
- [Sales Drawings - CGB239 Sales Drawing](#)
- [Specifications - CGB239 Specification Sheet French](#)
- [Specifications - CGB239 Specification Sheet English](#)
- [Video - CGB Series Introduction](#)