

By Killark

Catalog # [CGB355](#)

CGB Series - Unarmored Cable Connector 1" NPT Zinc Plated Steel



Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from 1/2"" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

Application

Suitable for use in Class I Divisions 2 when installed in accordance to NEC 501.10(B)(4). Approved for cable use including TC, TC-ER, TC-ER-HL, PLTC, PLTC-ER, ITC, ITC-HL and cords including S, SO, STO, ST, SJ, SJT, SJTO, SVO.

Conductor

Cable Range .551 - .945 in

Dimensions

Hub Size 1"

General

Series	CGB
Finish Name	Natural
Material	Steel
UPC	783936184586
Ingress Protection	Type 3R, 4, 4X, 12

Operational

Operating Temperature - 40C to +80 °C

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)