

## CGB486 - CGB Series - Unarmored Cable Connector 1-1/4" NPT Zinc Plated Steel

By Killark

Catalog # [CGB486](#)

The CGB connector is for use all unarmored cable and flexible cords. This connector features a removable "top-hat" sleeve seal and is designed to cover a broader range of cable diameters for carrying less stocking SKU's. Superior ingress protection with Type 3,3R,4,4X,12 ratings. Designed and certified for NEC and CEC applications.

### Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from 1/2"" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

### General

Catalog Number	CGB486
Finish Name	Natural
Ingress Protection	Type 3R, 4, 4X, 12
Material	Steel
Operating Temperature	- 40C to +80 °C
Series	CGB
UPC	783936184616

### Dimensions



Hub Size 1-1/4"

### Conductor Related

Cable Range .866 - 1.26 in

### Product Assets

[3D Models - CGB486 3D Model](#)

[3D Models - CGB486 3D Model](#)

[Brochures - Killark CGB Gland Flyer - English](#)

[Brochures - CGB Series A Revolutionary Cable Connector for Industrial and Hazardous Applications](#)

[Brochures - Killark CGB Gland Flyer - French](#)

[Catalog Page - CGB Glands Catalog](#)

[Catalogs - Killark Catalog](#)

[Certifications - KIL\\_CGB UL Certificate\\_UL](#)

[Engineering Drawing - CGB486 Engineering Drawing](#)

[Sales Drawings - CGB486 Sales Drawing](#)

[Specifications - CGB486 Specification Sheet French](#)

[Specifications - CGB486 Specification Sheet English](#)

[Video - CGB Series Introduction](#)