



CGB6102 - CGB Series - Unarmored Cable Connector 2" NPT Zinc Plated Steel

By Killark
Catalog # [CGB6102](#)

The CGB connector is for use all unarmored cable and flexible cords. This connector features a removable "top-hat" sleeve seal and is designed to cover a broader range of cable diameters for carrying less stocking SKU's. Superior ingress protection with Type 3,3R,4,4X,12 ratings. Designed and certified for NEC and CEC applications.

Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from 1/2" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

General

Catalog Number	CGB6102
Finish Name	Natural
Ingress Protection	Type 3R, 4, 4X, 12
Material	Steel
Operating Temperature	- 40C to +80 °C
Series	CGB
UPC	783936184661



Dimensions

Hub Size	2"
----------	----

Conductor Related

Cable Range	1.02 - 1.38 in
-------------	----------------

Product Assets

- [3D Models - CGB6102 3D Model](#)
- [3D Models - CGB6102 3D Model](#)
- [Brochures - CGB Series A Revolutionary Cable Connector for Industrial and Hazardous Applications](#)
- [Catalog Page - CGB Glands Catalog](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - KIL_CGB UL Certificate_UL](#)
- [Engineering Drawing - CGB6102 Engineering Drawing](#)
- [Sales Drawings - CGB6102 Sales Drawing](#)
- [Specifications - CGB6102 Specification Sheet French](#)
- [Specifications - CGB6102 Specification Sheet English](#)
- [Video - CGB Series Introduction](#)



A Hubbell brand