

COLB-4CG - 1-1/4" LB Hub, Aluminum Combo Conduit Body

By Killark

Catalog # **COLB-4CG**

1-1/4" LB Hub, Aluminum Combo Conduit Body



*Representative Image

Features

- Combination bodies have threaded and set screw hubs
- Prepackaged with body, cover, and gasket
- For use with IMC and EMT conduit
- Covers furnished with stainless steel screws
- NPSM threads
- Type 3 rated with Rigid / IMC conduit

Application

To provide access to conductors for pulling, splicing, maintenance, and for future changes or upgrades. Combination bodies for use with EMT or rigid/IMC conduit.

General

Catalog Number	COLB-4CG
Color	Gray
Cover Type	Stamped
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LB
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	CO
Type	Conduit Body With Cover & Gasket
UPC	783936067681

Dimensions

Dimensions	8 in x 3 in x 4 in
Gross Weight with Packaging	1.41
Height	4 in
Hub Size	1-1/4"
Length	8 in
Width	3 in

Certifications And Compliance

CSA File Number	LR11852
UL File Number	E3397

Logistics

Carton Quantity	2
-----------------	---

Product Assets

Catalogs - Killark Catalog
Certifications - E Series, O Series, CO & TW Series Conduit Bodies CSA Certificate of Conformity
Customer Notices - Prop 65 Notice
Specifications - COLB4CG Specification Sheet English
Specifications - CO-TWO Series Aluminum Conduit Bodies Specification Sheet
Specifications - COLB-4CG Specification Sheet French