



DBF3212-WL - DBF Series 32W T8 Electronic Ballast with Lamp

By Killark
Catalog # [DBF3212-WL](#)



DBF Series 32W T8 Electronic Ballast with Lamp

Features

- Sheet steel 20 ga. housing with continuous weld prevents foreign matter from entering enclosure.
- Lens frame assembly has silicon rubber gasketing and heat tempered glass lens.
- Electrostatically applied polyester finish.

General

Catalog Number	DBF3212-WL
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	T8
Light Source	Linear Fluorescent
Material	Steel
Mounting Type	Pendant
Optic Type	Glass Lens
Series	DBF
UPC	783936026879

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	32 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_DBF32x2](#)
- [Specifications - DBF3212WL Specification Sheet English](#)
- [Specifications - DBF3212-WL Specification Sheet French](#)
- [Specifications - DBF Series Specification Sheet](#)