



DEDS-30 - DEDS Series, 30 Amp Non-Fused Disconnect Switch

By Killark
Catalog # [DEDS-30](#)

DEDS Series, 30 Amp Non-Fused Disconnect Switch.



Features

- Eaton (Cutler-Hammer) Type DS Switches.
- Two cast conduit hubs, one top and one bottom.
- Internal disconnect handle mechanism is a sliding plate mounted to the cover.

General

Catalog Number	DEDS-30
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Number Of Poles	3
Operating Temperature Celcius Max	40 Degree
Series	DEDS
Type	
UPC	783936116426

Dimensions

Depth	6.875
Height	12.125 in
Weight	14.5 lb
Width	7.375 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 VAC/250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3R, 4, 9(E, F, G)
UL File Number	E53290

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - DEDS & XEDS Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-DEDS30-SPEC-EN | REV 6/2024