

ECF-18

By Killark
Catalog # [ECF-18](#)

1/2" Flexible Coupling with 8" Bend Length, Bronze.



*Representative Image

Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory

Application

For use in hazardous areas where movement or vibration requires a flexible connection or a difficult bend is required in a conduit system.

General

Color	<ul style="list-style-type: none">• Bronze• Bronze
Finish Type	Naturel
Material	Bronze
Series	ECF
Type	<ul style="list-style-type: none">• Flexible Coupling• Flexible Coupling
UPC	783936104102

Dimensions

Dimensions	13.25 in x 2.5 in x 2.5 in
Gross Weight with Packaging	1.82
Height	2.5 in
Hub Size	1/2"
Length	13.25 in
Width	2.5 in

Certifications and Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class I, Zones 1 & 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

[Catalogs - Killark Catalog](#)
[Certifications - ECF Series Flexible Couplings UL Certification](#)
[Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
[Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - ECF & EKJ Series IOM K1480](#)