



ECF-112 - 1/2" Flexible Coupling with 12" Bend Length, Bronze

By Killark
Catalog # [ECF-112](#)

1/2" Flexible Coupling with 12" Bend Length, Bronze



*Representative Image

Features

-
-
-
-
-

General

Catalog Number	ECF-112
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Material	Bronze
Series	ECF
UPC	783936105024

Dimensions

Dimensions	17.5 in x 2.75 in x 2.75 in
Gross Weight with Packaging	2.15
Height	2.75 in
Hub Size	1/2"
Length	17.5 in
Width	2.75 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
- [Certifications - ECF Series Flexible Couplings UL Certification](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - ECF & EKJ Series IOM K1480](#)
- [Specifications - ECF112 Specification Sheet English](#)
- [Specifications - ECF-EKJ Series Flexible Couplings Specification Sheet](#)
- [Specifications - ECF-112 Specification Sheet French](#)