

ECF-124 - 1/2" Flexible Coupling with 24" Bend Length, Bronze

By Killark

Catalog # [ECF-124](#)

1/2" Flexible Coupling with 24" Bend Length, Bronze



*Representative Image

Features

-
-
-
-
-

General

| | |
|-------------------|----------------------|
| Catalog Number | ECF-124 |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type | Natural |
| Material | Bronze |
| Series | ECF |
| UPC | 783936105109 |

Dimensions

| | |
|-----------------------------|-----------------------------|
| Dimensions | 29.125 in x 2.5 in x 2.5 in |
| Gross Weight with Packaging | 3 |
| Height | 2.5 in |
| Hub Size | 1/2" |
| Length | 29.125 in |
| Width | 2.5 in |

Certifications And Compliance

| | |
|---------------------|---|
| CSA File Number | LR11716 |
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class I, Zones 1 & 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2 |
| UL File Number | E10514 |

Product Assets

| |
|--|
| Catalogs - Killark Catalog |
| Certifications - ECF, EKJ, EKJSS Series UKCA Certification |
| Certifications - ECF Series Flexible Couplings UL Certification |
| Certifications - ECF/EKJ Flexible Couplings CSA Certification |
| Customer Notices - Prop 65 Notice |
| Installation Manuals - ECF & EKJ Series IOM K1480 |
| Specifications - ECF-EKJ Series Flexible Couplings Specification Sheet |
| Specifications - ECF124 Specification Sheet English |
| Specifications - ECF-124 Specification Sheet French |