



ECF-136 - 1/2" Flexible Coupling with 36" Bend Length, Bronze

By Killark
Catalog # [ECF-136](#)



1/2" Flexible Coupling with 36" Bend Length, Bronze.

*Representative Image

Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory

General

Application	
Catalog Number	ECF-136
Color	Bronze
	Bronze
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Bronze
Series	ECF
Type	
UPC	783936105147

Dimensions

Dimensions	41.5 in x 2.5 in x 2.5 in
Gross Weight with Packaging	3.86
Height	2.5 in
Hub Size	1/2"
Length	41.5 in
Width	2.5 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, D
	Class I, Zones 1 & 2, Groups IIC, IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

[Catalogs - Killark Catalog](#)
[Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
[Certifications - ECF Series Flexible Couplings UL Certification](#)
[Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - ECF & EKJ Series IOM K1480](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-ECF136-SPEC-EN | REV 6/2024