

## ECF-16 - Raccord flexible 1/2" avec longueur de coude 6", bronze

Par Killark  
No de catalogue [ECF-16](#)

Coupleur flexible 1/2" avec une longueur de courbure de 6", bronze.



\*Image représentative

### Général

Numéro de catalogue	ECF-16
Couleur	
Indicateur RoHS de l'UE	Contacter le fabricant
Type de finition	Naturel
Matériau	Bronze
Série	ECF
Type	
CUP	783936104058

### Dimensions

Dimensions	12,125 po x 2,75 po x 2,75 po
Poids brut avec emballage	1.75
Hauteur	2.75 in
Taille du moyeu	1/2"
Longueur	12.125 en
Largeur	2.75 in

### Certifications et conformité

Numéro de dossier CSA	LR11716
Cote(s) de dangerosité	<ul style="list-style-type: none"><li>• Classe I, divisions 1 et 2, groupes A, B, C, D</li><li>• Classe I, zones 1 et 2, groupes IIC, IIB, IIA</li><li>• Classe II, divisions 1 et 2, groupes E, F, G</li><li>• Classe III, divisions 1 et 2</li></ul>
Numéro de dossier UL	E10514

### Documentation

- [Avis aux clients - Prop 65 Notice](#)
- [Catalogues - Killark Catalog](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Certifications - ECF Series Flexible Couplings UL Certification](#)
- [Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
- [Manuels d'installation - ECF & EKJ Series IOM K1480](#)
- [Spécifications - ECF-16](#)
- [Spécifications - ECF-EKJ Series Flexible Couplings Specification Sheet](#)
- [Spécifications - ECF-16](#)