

ECF-18 - Coupleur flexible 1/2" avec une longueur de coude de 8", bronze

Par Killark

No de catalogue [ECF-18](#)

Coupleur flexible 1/2" avec une longueur de coude de 8", bronze.



*Image représentative

Général

Numéro de catalogue	ECF-18
Couleur	
Indicateur RoHS de l'UE	Contacter le fabricant
Type de finition	Naturel
Matériau	Bronze
Série	ECF
Type	
CUP	783936104102

Dimensions

Dimensions	13.25 in x 2.5 in x 2.5 in
Poids brut avec emballage	1.82
Hauteur	2.5 in
Taille du moyeu	1/2"
Longueur	13,25 pouces
Largeur	2.5 in

Certifications et conformité

Numéro de dossier CSA	LR11716
Cote(s) de dangerosité	<ul style="list-style-type: none">• Classe I, divisions 1 et 2, groupes A, B, C, D• Classe I, zones 1 et 2, groupes IIC, IIB, IIA• Classe II, divisions 1 et 2, groupes E, F, G• Classe III, divisions 1 et 2
Numéro de dossier UL	E10514

Documentation

[Avis aux clients - Prop 65 Notice](#)
[Catalogues - Killark Catalog](#)
[Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
[Certifications - ECF Series Flexible Couplings UL Certification](#)
[Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
[Manuels d'installation - ECF & EKJ Series IOM K1480](#)
[Spécifications - ECF-18](#)
[Spécifications - ECF-18](#)
[Spécifications - ECF-EKJ Series Flexible Couplings Specification Sheet](#)