



## ECF-215 - 3/4" Flexible Coupling with 15" Bend Length, Bronze

By Killark  
Catalog # [ECF-215](#)



3/4" Flexible Coupling with 15" Bend Length, Bronze.

\*Representative Image

### Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory

### General

Application	
Catalog Number	ECF-215
Color	Bronze
	Bronze
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Bronze
Series	ECF
Type	
UPC	783936105208

### Dimensions

Dimensions	25 in x 2.25 in x 2.5 in
Gross Weight with Packaging	3.5
Height	2.5 in
Hub Size	3/4"
Length	25 in
Width	2.25 in

### Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, D
	Class I, Zones 1 & 2, Groups IIC, IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E10514

### Product Assets

[Catalogs - Killark Catalog](#)  
[Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)  
[Certifications - ECF Series Flexible Couplings UL Certification](#)  
[Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - ECF & EKJ Series IOM K1480](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-ECF215-SPEC-EN | REV 6/2024