

ECF-224 - Coupleur flexible 3/4" avec une longueur de coude de 24", bronze

Par Killark

No de catalogue [ECF-224](#)

Coupleur flexible de 3/4" avec une longueur de courbure de 24", bronze.



*Image représentative

Général

Numéro de catalogue	ECF-224
Couleur	
Indicateur RoHS de l'UE	Contacter le fabricant
Type de finition	Naturel
Matériau	Bronze
Série	ECF
Type	
CUP	783936105239

Dimensions

Dimensions	29,5 in x 2,5 in x 2,5 in
Poids brut avec emballage	4.27
Hauteur	2.5 in
Taille du moyeu	3/4"
Longueur	29.5 in
Largeur	2.5 in

Certifications et conformité

Numéro de dossier CSA	LR11716
Cote(s) de dangerosité	<ul style="list-style-type: none">• Classe I, divisions 1 et 2, groupes A, B, C, D• Classe I, zones 1 et 2, groupes IIC, IIB, IIA• Classe II, divisions 1 et 2, groupes E, F, G• Classe III, divisions 1 et 2
Numéro de dossier UL	E10514

Documentation

[Avis aux clients - Prop 65 Notice](#)
[Catalogues - Killark Catalog](#)
[Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
[Certifications - ECF Series Flexible Couplings UL Certification](#)
[Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
[Manuels d'installation - ECF & EKJ Series IOM K1480](#)
[Spécifications - ECF-224](#)
[Spécifications - ECF-224](#)
[Spécifications - ECF-EKJ Series Flexible Couplings Specification Sheet](#)