

ECF-312 - Raccord flexible 1" avec une longueur de coude de 12", bronze

Par Killark

No de catalogue [ECF-312](#)

Coupleur flexible 1" avec une longueur de courbure de 12", bronze.



*Image représentative

Général

Numéro de catalogue	ECF-312
Couleur	
Indicateur RoHS de l'UE	Contacter le fabricant
Type de finition	Naturel
Matériau	Bronze
Série	ECF
Type	
CUP	783936105307

Dimensions

Dimensions	18.25 in x 2.5 in x 2.25 in
Poids brut avec emballage	4.01
Hauteur	2.25 in
Taille du moyeu	1"
Longueur	18.25 in
Largeur	2.5 in

Certifications et conformité

Numéro de dossier CSA	LR11716
Cote(s) de dangerosité	<ul style="list-style-type: none">• Classe I, divisions 1 et 2, groupes A, B, C, D• Classe I, zones 1 et 2, groupes IIC, IIB, IIA• Classe II, divisions 1 et 2, groupes E, F, G• Classe III, divisions 1 et 2
Numéro de dossier UL	E10514

Documentation

- [Avis aux clients - Prop 65 Notice](#)
- [Catalogues - Killark Catalog](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Certifications - ECF Series Flexible Couplings UL Certification](#)
- [Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
- [Manuels d'installation - ECF & EKJ Series IOM K1480](#)
- [Spécifications - ECF-312](#)
- [Spécifications - ECF-EKJ Series Flexible Couplings Specification Sheet](#)
- [Spécifications - ECF-312](#)