



ECF-315 - 1" Flexible Coupling with 15" Bend Length, Bronze

By Killark
Catalog # [ECF-315](#)



1" Flexible Coupling with 15" Bend Length, Bronze.

*Representative Image

Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory

General

Application	
Catalog Number	ECF-315
Color	Bronze
	Bronze
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Bronze
Series	ECF
Type	
UPC	783936105314

Dimensions

Dimensions	21 in x 15 in x 2 in
Gross Weight with Packaging	4.5
Height	2 in
Hub Size	1"
Length	21 in
Width	15 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, D
	Class I, Zones 1 & 2, Groups IIC, IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Certifications - ECF Series Flexible Couplings UL Certification](#)
- [Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - ECF & EKJ Series IOM K1480](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-ECF315-SPEC-EN | REV 6/2024