



ECF-324 - 1" Flexible Coupling with 24" Bend Length, Bronze

By Killark
Catalog # [ECF-324](#)



1" Flexible Coupling with 24" Bend Length, Bronze.

*Representative Image

Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory

General

Application	
Catalog Number	ECF-324
Color	Bronze
	Bronze
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Bronze
Series	ECF
Type	
UPC	783936105406

Dimensions

Dimensions	30.25 in x 2.25 in x 2.625 in
Gross Weight with Packaging	5.53
Height	2.625 in
Hub Size	1"
Length	30.25 in
Width	2.25 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, D
	Class I, Zones 1 & 2, Groups IIC, IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Certifications - ECF Series Flexible Couplings UL Certification](#)
- [Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - ECF & EKJ Series IOM K1480](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-ECF324-SPEC-EN | REV 6/2024