



# ECF-38 - 1" Flexible Coupling with 8" Bend Length, Bronze

By Killark  
Catalog # [ECF-38](#)

1" Flexible Coupling with 8" Bend Length, Bronze



\*Representative Image

### Features

- 
- 
- 
- 
- 

### Application

For use in hazardous areas where movement or vibration requires a flexible connection or a difficult bend is required in a conduit system.

### General

Catalog Number	ECF-38
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Material	Bronze
Series	ECF
Type	Flexible Coupling
UPC	783936104355

### Dimensions

Dimensions	14 in x 2.5 in x 2.5 in
Gross Weight with Packaging	3.63
Height	2.5 in

Hub Size	1"
Length	14 in
Width	2.5 in

### Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Divisions 1 &amp; 2, Groups A, B, C, D</li> <li>• Class I, Zones 1 &amp; 2, Groups IIC, IIB, IIA</li> <li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
UL File Number	E10514

### Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - ECF, EKJ, EKJSS Series UKCA Certification](#)
- [Certifications - ECF Series Flexible Couplings UL Certification](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - ECF & EKJ Series IOM K1480](#)
- [Specifications - ECF-EKJ Series Flexible Couplings Specification Sheet](#)
- [Specifications - ECF38 Specification Sheet English](#)
- [Specifications - ECF-38 Specification Sheet French](#)