



ECFUF-224 - 3/4" Flexible Coupling with 24" Bend Length, Bronze

By Killark
Catalog # [ECFUF-224](#)

3/4" Flexible Coupling with 24" Bend Length, Bronze



*Representative Image

Features

-
-
-
-

General

Catalog Number	ECFUF-224
Color	Bronze
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Material	Bronze
Series	ECFUF
UPC	783936105765

Dimensions

Gross Weight with Packaging	5.5
Hub Size	3/4"

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - ECF/EKJ Flexible Couplings CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - ECF & EKJ Series IOM K1480](#)
- [Specifications - ECFUF224 Specification Sheet English](#)
- [Specifications - ECFUF-EKJUF Series Flexible Couplings Specification Sheet](#)
- [Specifications - ECFUF-224 Specification Sheet French](#)