



EMH050 - EM Series - Aluminum 50 Watt Medium Base Metal Halide Light Fixture -Quadri-Volt (120/208/240/277V) At 60Hz

By Killark
Catalog # EMH050



EM Series - Aluminum 50 Watt Medium Base Metal Halide Light Fixture -Quadri-Volt (120/208/240/277V) At 60Hz.

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EMH050
Color	<ul style="list-style-type: none">• Tan• bronzer
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Mogul Base
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Fluted
Reflector Type	Specular Aluminum
Series	EM
Type	
UPC	783936149301

Dimensions

Dimensions	8.69 in x 15.75 in x 8.69 in
Gross Weight with Packaging	19
Height	8.69 in
Length	8.69 in
Width	15.75 in

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	50 W

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_EM Series HID Luminaires IOM_K1114](#)
- [Photometry - KIL_EMH05x-S](#)
- [Photometry - KIL_EMH05x](#)
- [Photometry - KIL_EMH05x-A](#)
- [Specifications - EMH050 Specification Sheet French](#)
- [Specifications - EM-EQ Series Specification Sheet](#)