



EMH050A3 - 50W Metal Halide 1" Pendant

By Killark
Catalog # [EMH050A3](#)

50W Metal Halide 1" Pendant

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EMH050A3
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Light Source	Metal Halide
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Pendant
Optic Type	Glass Globe - Fluted
Series	EM
UPC	783936135267



Dimensions

Hub Size	1"
----------	----

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	50 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_EMH05x-A](#)
- [Photometry - KIL_EMH05x](#)
- [Photometry - KIL_EMH05x-S](#)
- [Specifications - EM-EQ Series Specification Sheet](#)
- [Specifications - EMH050A3 Specification Sheet French](#)
- [Specifications - EMH050A3 Specification Sheet English](#)