



EMH050 CEN - 50W Metal Halide-Quadri-Volt, ATEX Rated

By Killark
Catalog # [EMH050 CEN](#)

50W Metal Halide- Quadri-Volt, ATEX Rated

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EMH050 CEN
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Material	Aluminum, Copper Free (less than 4/10 of 1%)



Optic Type	Glass Globe - Fluted
Series	EM
UPC	783936129044

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	50 W

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_EM Series HID Luminaires IOM_K1114](#)
- [Photometry - KIL_EMH05x-A](#)
- [Photometry - KIL_EMH05x](#)
- [Photometry - KIL_EMH05x-S](#)
- [Specifications - EMH050 CEN Specification Sheet French](#)
- [Specifications - EMH050CEN Specification Sheet English](#)
- [Specifications - EM-EQ Series Specification Sheet](#)



A Hubbell brand