



# EMH100B2G - CLI 100W Metal Halide 3/4" Bracket Mount with Guard

By Killark  
Catalog # [EMH100B2G](#)

CLI 100W Metal Halide 3/4" Bracket Mount with Guard

## Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

## General

Catalog Number	EMH100B2G
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Optic Type	Glass Globe - Fluted
Series	EM
UPC	783936148199



## Dimensions

Hub Size	3/4"
----------	------

## Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	100 W

## Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
---------------------	--

## Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL\\_EMH10x-S](#)
- [Photometry - KIL\\_EMH10x-A](#)
- [Photometry - KIL\\_EMH10x](#)
- [Specifications - EMH100B2G Specification Sheet French](#)
- [Specifications - EM-EQ Series Specification Sheet](#)
- [Specifications - EMH100B2G Specification Sheet English](#)



A Hubbell brand