



EMI30 - EMI Series - Aluminum 300W Incandescent Light Fixture - 250VAC Max

By Killark
Catalog # [EMI30](#)

EMI Series - Aluminum 300W Incandescent Light Fixture -
250VAC Max

Features

-
-
-
-
-
-
-

General

Catalog Number	EMI30
Color	Tan
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Cycles	10,000 hrs
Optic Type	Glass Globe - Fluted
Series	EM
UPC	783936149295

Dimensions

Dimensions	12.125 in x 10.25 in x 9.875 in
Gross Weight with Packaging	13.68
Height	9.875 in
Length	12.125 in



Width	10.25 in
-------	----------

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120-277 VAC
Wattage	300 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_EMI-EBF-EQF Series Luminaires IOM_K1094](#)
- [Photometry - KIL_EMI30-S](#)
- [Photometry - KIL_EMI30](#)
- [Photometry - KIL_EMI30-A](#)
- [Specifications - EM-EQ Series Specification Sheet](#)
- [Specifications - EMI30 Specification Sheet English](#)
- [Specifications - EMI30 Specification Sheet French](#)