



EMI30X2G - Incandescent 2/300W 3/4" Ceiling Mount with Guard

By Killark
Catalog # EMI30X2G

Incandescent 2/300W 3/4" Ceiling Mount with Guard.



Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EMI30X2G
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Medium Base
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Fluted
Series	EM
UPC	783936148038

Dimensions

Hub Size 3/4"

Electrical Ratings

Frequency Rating 60 Hz
Voltage Rating 120-277 VAC
Wattage 300 W

Certifications And Compliance

Hazardous Rating(s)

- Class I, Divisions 1 & 2, Groups C, D
- Class I, Zones 1 & 2, Groups IIB, IIA
- Class II, Divisions 1 & 2, Groups E, F, G
- Class III, Divisions 1 & 2

Logistics

Carton Quantity 1

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Photometry - KIL_EMI30-S](#)
[Photometry - KIL_EMI30](#)
[Photometry - KIL_EMI30-A](#)
[Specifications - EM-EQ Series Specification Sheet](#)
[Specifications - EMI30X2G Specification Sheet French](#)