



EMS100 - EM Series - Aluminum 100W Medium Base High Pressure Sodium Light Fixture (Lamp Not Included) - Quadri-Volt (120/208/240/277V) At 60Hz

By Killark
Catalog # EMS100

EM Series - Aluminum 100W Medium Base High Pressure Sodium Light Fixture (Lamp Not Included) - Quadri-Volt (120/208/240/277V) At 60Hz

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EMS100
Color	Tan
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Light Source	High Pressure Sodium
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Luminaire Only
Optic Type	Glass Globe - Fluted
Series	EM
Type	Aluminum High Pressure Sodium Fixture
UPC	783936149424



Dimensions

Dimensions	8.687 in x 8.687 in x 14.75 in
Gross Weight with Packaging	19
Height	14.75 in
Length	8.687 in
Width	8.687 in

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	100 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_EM Series HID Luminaires IOM_K1114](#)
- [Photometry - KIL_EMS10x-A](#)
- [Photometry - KIL_EMS10x](#)
- [Photometry - KIL_EMS10x-S](#)
- [Specifications - EM-EQ Series Specification Sheet](#)
- [Specifications - EMS100 Specification Sheet French](#)
- [Specifications - EMS100 Specification Sheet English](#)



A Hubbell brand