



EMS151D4 - HID 150W Fluorescent 120V HPS 1-1/4" Stanchion Mount

By Killark
Catalog # [EMS151D4](#)

HID 150W Fluorescent 120V HPS 1-1/4" Stanchion Mount

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

| | |
|-------------------|--|
| Catalog Number | EMS151D4 |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type | Powder Epoxy Paint |
| Lamp Type | Medium Base |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| Optic Type | Glass Globe - Fluted |
| Series | EM |
| UPC | 783936136332 |



Dimensions

| | |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

Electrical Ratings

| | |
|------------------|---------|
| Frequency Rating | 60 Hz |
| Voltage Rating | 120 VAC |
| Wattage | 150 W |

Certifications And Compliance

| | |
|---------------------|--|
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2 |
|---------------------|--|

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Photometry - KIL_EMS15x-A](#)
[Photometry - KIL_EMS15x](#)
[Photometry - KIL_EMS15x-S](#)
[Specifications - EMS151D4 Specification Sheet English](#)
[Specifications - EM-EQ Series Specification Sheet](#)
[Specifications - EMS151D4 Specification Sheet French](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
KILL_CA-EMS151D4-SPEC-EN | REV 4/2025