



EMS351 - EM Series - Aluminum 35W Medium Base High Pressure Sodium Light Fixture - 120V At 60Hz

By Killark
Catalog # EMS351



EM Series - Aluminum 35W Medium Base High Pressure Sodium Light Fixture - 120V At 60Hz.

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EMS351
Color	<ul style="list-style-type: none"> • Tan • bronzer
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Medium Base
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Fluted
Series	EM
Type	
UPC	783936149387

Dimensions

Dimensions	8.69 in x 15.75 in x 8.69 in
Gross Weight with Packaging	15
Height	8.69 in
Length	8.69 in
Width	15.75 in

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120 VAC
Wattage	35 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_EM Series HID Luminaires IOM_K1114](#)
- [Photometry - KIL_EMS35x-S](#)
- [Photometry - KIL_EMS35x](#)
- [Photometry - KIL_EMS35x-A](#)
- [Specifications - EM-EQ Series Specification Sheet](#)
- [Specifications - EMS351 Specification Sheet French](#)