



EQF3230B2G

By Killark
Catalog # [EQF3230B2G](#)

32W Fluorescent 120-277V 3/4" Wall Mount with Guard.



Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware is 316 grade stainless steel.

General

Finish Type	Peinture époxy en poudre
Lamp Type	Quad Pin
Light Source	Compact Fluorescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall Bracket
Optic Type	Glass Globe - Clear
Series	EQF
UPC	783936143484

Dimensions

Hub Size 3/4"

Electrical Ratings

Frequency Rating 50/60 Hz
Voltage Rating 120-277 VAC
Wattage 32 W

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	--

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Photometry - KIL_EQF32x-S](#)
[Photometry - KIL_EQF32x](#)
[Photometry - KIL_EQF32x-A](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-EQF3230B2G-SPEC-EN | REV 1/2024