



## ESXR120AB2G - 120V Red Strobe, 3/4" Bracket Mount with Guard

By Killark

Catalog # [ESXR120AB2G](#)

120V Red Strobe, 3/4" Bracket Mount with Guard.



### Features

- Electronic component temperature range -40°C to +55°C
- NEC temperature code, T6 (<85°C)
- Flash rate-85 flashes per minute
- Xenon type lamp
- Voltage and amperage: 12-74 VDC: Draws 1.25A avg. @ 12 VDC tapering to 0.2A avg. @ 74 VDC, .75A avg. @ 24 VDC
- 120 VAC (50/60 HZ): Draws 0.30A avg.
- 240 VAC (50/60 HZ): Draws 0.17A avg.
- Power supply output: 13 watts standard 11 watts for 12-74 VDC

### General

Catalog Number	ESXR120AB2G
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Flashing
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Red
Series	ESX
UPC	783936106519

### Dimensions

Hub Size	3/4"
----------	------

### Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120 VAC

### Certifications And Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class I, Zones 1 & 2, Groups IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2

### Product Assets

[Certifications - ESX Series UL Certification](#)

[Customer Notices - Prop 65 Notice](#)

[Installation Manuals - KIL\\_ESX Series Signal Luminaire IOM\\_K1121](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-ESXR120AB2G-SPEC-EN | REV 6/2024