



# EXB-NFD-0303P - EXB-NFD Series, AL Non Fused Disconnect Switch, Switch Rating 30- 3-Pole - Top Conduit 2", Bottom Conduit 1/2", Wire Size 14-4

By Killark  
Catalog # [EXB-NFD-0303P](#)

EXB-NFD Series - Aluminum Non Fused Disconnect Switch - Switch Rating 30- 3-Pole - Top Conduit 2 Inch - Bottom Conduit 1/2 Inch - Wire Size 14-4.



\*Representative Image

## Features

- Copper-free aluminum construction, high strength, lighter in weight and corrosion resistant.
- Fewer cover bolts (no corner bolts required) reduces installation and maintenance time.
- Cover bolts are stainless steel.
- Gasketed flange with O-ring located inside the bolt circle to seal out moisture.
- Stainless steel hinges are standard.
- Switch operating handle of copper-free aluminum can be padlocked, with up to three locks, in either the "ON" or "OFF" position.
- Ductile mounting lugs adjust to irregular mounting surfaces.
- Bodies have top and bottom drilled and taped conduit entrances for power and drain/breather.
- Global applications (ATEX) Enclosures are available for global applications with "CEN" suffix.
- Assemblies that are modified to CENELEC/ATEX standards maintain their North American certifications.

## Application

- EXB-NFD Series hinged cover disconnect switches are used: in locations made hazardous due to the presence of flammable gasses or vapors or ignitable dusts, fibers, and flyings
- outdoors or indoors in damp, wet, and dirty locations
- or in areas where frequent washdowns, heavy rain, or water spray routinely occurs.

## General

Actuator	Handle
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall
Number Of Poles	3
Operating Temperature Celcius Max	40 Degree
Series	EXB-NFD
Size	8" x 8" x 6"
Type	<ul style="list-style-type: none"> <li>• Aluminum Non-Fused</li> </ul>

## Dimensions

Depth	4
Dimensions	14.06 in x 10.3 in x 10.3 in
Gross Weight with Packaging	40
Height	10.3 in
Length	14.06 in
Weight	40 lb
Width	10.3 in

## Electrical Ratings

Amperage Rating	30 A
Frequency Rating	60 Hz
Primary Voltage	600 VAC

## Conductor Related

Number Of Wires	4
-----------------	---

## Certifications and Compliance

ATEX File Number	PTB 07 ATEX 1024x
CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li> <li>• Class I, Zones 1 &amp; 2, Groups IIB+H2, IIA</li> <li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
Nema Rating	3, 4, 4X, 7(B, C, D), 9(E, F, G)
UL File Number	E10514 / E83969 / E12379

## Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - EXB/LT-FDS & NFD IOM K1517](#)

Type

Aluminum Non-Fused  
Disconnect Switch

- Aluminum Non-Fused  
Disconnect Switch

UPC

783936012179



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-EXB-NFD-0303P-SPEC-EN | REV 1/2024