



EXB-NFD-2003P - EXB-NFD Series, 200 Amp 3-Pole , Non-Fused Disconnect Switch

By Killark
Catalog # [EXB-NFD-2003P](#)

EXB-NFD Series, 200 Amp 3-Pole , Non-Fused Disconnect Switch.



*Representative Image

Features

- Copper-free aluminum construction, high strength, lighter in weight and corrosion resistant.
- Fewer cover bolts (no corner bolts required) reduces installation and maintenance time.
- Cover bolts are stainless steel.
- Gasketed flange with O-ring located inside the bolt circle to seal out moisture.
- Stainless steel hinges are standard.
- Switch operating handle of copper-free aluminum can be padlocked, with up to three locks, in either the "ON" or "OFF" position.
- Ductile mounting lugs adjust to irregular mounting surfaces.
- Bodies have top and bottom drilled and taped conduit entrances for power and drain/breather.
- Global applications (ATEX) Enclosures are available for global applications with "CEN" suffix.
- Assemblies that are modified to CENELeC/ATEX standards maintain their North American certifications.

Application

- EXB-NFD Series hinged cover disconnect switches are used: in locations made hazardous due to the presence of flammable gasses or vapors or ignitable dusts, fibers, and flyings
- outdoors or indoors in damp, wet, and dirty locations
- or in areas where frequent washdowns, heavy rain, or water spray routinely occurs.

General

EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall
Operating Temperature Celcius Max	40 Degree
Series	EXB-NFD
Size	12" x 24" x 8"
Type	<ul style="list-style-type: none"> • Non-Fused Disconnect • Non-Fused Disconnect
UPC	783936132310

Dimensions

Depth	15.9375
Height	28.375 in
Weight	170 lb
Width	16.375 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 VAC

Certifications and Compliance

ATEX File Number	PTB 07 ATEX 1024x
CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X, 7(B, C, D), 9(E, F, G)
UL File Number	E10514 / E83969 / E12379

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - EXB Series Drilling & Tapping IOM K1156](#)
- [Installation Manuals - EXB/LT-FDS & NFD IOM K1517](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-EXB-NFD-2003P-SPEC-EN | REV 1/2024