



## EXB-NFD-2003P - EXB-NFD Series, 200 Amp 3-Pole , Non-Fused Disconnect Switch

By Killark  
Catalog # EXB-NFD-2003P

EXB-NFD Series, 200 Amp 3-Pole , Non-Fused Disconnect Switch.



### Features

Assemblies that are modified to CENELEC/ATEX standards maintain their North American certifications.

### General

Application	
Catalog Number	EXB-NFD-2003P
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Operating Temperature Celcius	40 Degree
Max	
Series	EXB-NFD
Size	12" x 24" x 8"
Type	
UPC	783936132310

### Dimensions

Depth	15.9375
Height	28.375 in
Weight	170 lb
Width	16.375 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 VAC

### Certifications And Compliance

ATEX File Number	PTB 07 ATEX 1024x
CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X, 7(B, C, D), 9(E, F, G)
UL File Number	E10514 / E83969 / E12379

### Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - EXB Series Drilling & Tapping IOM K1156](#)
- [Installation Manuals - EXB/LT-FDS & NFD IOM K1517](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-EXBNFD2003P-SPEC-EN | REV 6/2024