



EZS150A2-T - HID 150W Quadri-Volt High Pressure Sodium 3/4" Trunnion Mount

By Killark
Catalog # [EZS150A2-T](#)

HID 150W Quadri-Volt High Pressure Sodium 3/4" Trunnion Mount.



Features

- Trunnion mounted—Trunnion yoke of 316 grade stainless steel attaches via mounting blocks to fixture ballast housing
- Factory sealed—No external seal needed
- Corrosion resistant—Fixture of copper-free aluminum die cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware of 316 grade stainless steel
- Accessories—Guards, reflectors and mounting hardware available. Must be ordered separately.

General

Finish Type	Peinture époxy en poudre
Lamp Type	Mogul Base
Light Source	High Pressure Sodium
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Trunnion
Optic Type	Glass Globe - Clear
Series	EZ
UPC	783936097718

Dimensions

Hub Size 3/4"

Electrical Ratings

Frequency Rating 60 Hz
Voltage Rating Quad - 120/277/347/480 VAC
Wattage 150 W

Certifications and Compliance

Hazardous Rating(s)

- Class I, Divisions 1 & 2, Groups C, D
- Class I, Zones 1 & 2, Groups IIB, IIA

Product Assets

[Certifications - EZ Series Luminaries CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Photometry - KIL_EZS15x-D](#)
[Photometry - KIL_EZS15x-A](#)
[Photometry - KIL_EZS15x](#)
[Photometry - KIL_EZS15x-S](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-EZS150A2-T-SPEC-EN | REV 1/2024