



EZS150A2-T - HID 150W Quadri-Volt High Pressure Sodium 3/4" Trunnion Mount

By Killark
Catalog # EZS150A2-T



HID 150W Quadri-Volt High Pressure Sodium 3/4" Trunnion Mount.

Features

Accessories—Guards, reflectors and mounting hardware available. Must be ordered separately.

General

| | |
|-------------------|--|
| Catalog Number | EZS150A2-T |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type | Peinture époxy en poudre |
| Lamp Type | Mogul Base |
| Light Source | |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| Mounting Type | |
| Optic Type | Glass Globe - Clear |
| Series | EZ |
| UPC | 783936097718 |

Dimensions

| | |
|----------|------|
| Hub Size | 3/4" |
|----------|------|

Electrical Ratings

| | |
|------------------|----------------------------|
| Frequency Rating | 60 Hz |
| Voltage Rating | Quad - 120/277/347/480 VAC |
| Wattage | 150 W |

Certifications And Compliance

| | |
|---------------------|--|
| Hazardous Rating(s) | <ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA |
|---------------------|--|

Product Assets

- [Certifications - EZ Series Luminaries CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_EZS15x-A](#)
- [Photometry - KIL_EZS15x-D](#)
- [Photometry - KIL_EZS15x](#)
- [Photometry - KIL_EZS15x-S](#)
- [Specifications - EZ Series Floodlight Specification Sheet](#)
- [Specifications - EZS150A2-T Specification Sheet French](#)