



EZS400A2-T - HID 400W Quadri-Volt High Pressure Sodium 3/4" Pendant with Guard Trunnion Mount

By Killark
Catalog # [EZS400A2-T](#)

HID 400W Quadri-Volt High Pressure Sodium 3/4" Pendant with Guard Trunnion Mount.



Features

Accessories—Guards, reflectors and mounting hardware available. Must be ordered separately.

General

Catalog Number	EZS400A2-T
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Mogul Base
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Clear
Series	EZ
UPC	783936097756

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	400 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> Class I, Divisions 1 & 2, Groups C, D Class I, Zones 1 & 2, Groups IIB, IIA
---------------------	--

Product Assets

- [Certifications - EZ Series Luminaries CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_EZS40x-D](#)
- [Photometry - KIL_EZS40x-A](#)
- [Photometry - KIL_EZS40x-S](#)
- [Photometry - KIL_EZS40x](#)
- [Specifications - EZ Series Floodlight Specification Sheet](#)
- [Specifications - EZS400A2-T Specification Sheet French](#)