



EZS405A2-T - HID 400W 480V High Pressure Sodium 3/4" Pendant with Trunnion Mount

By Killark
Catalog # [EZS405A2-T](#)

HID 400W 480V High Pressure Sodium 3/4" Pendant with
Trunnion Mount

Features

- Trunnion mounted–Trunnion yoke of 316 grade stainless steel attaches via mounting blocks to fixture ballast housing
- Factory sealed–No external seal needed
- Corrosion resistant–Fixture of copper-free aluminum die cast construction. Baked powder epoxy finish, electro-statically applied. Exposed hardware of 316 grade stainless steel
- Accessories–Guards, reflectors and mounting hardware available. Must be ordered separately.

General

Catalog Number	EZS405A2-T
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Mogul Base
Light Source	High Pressure Sodium
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Trunnion
Optic Type	Glass Globe - Clear
Series	EZ
UPC	783936097763

Dimensions



Hub Size3/4"

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	400 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA
---------------------	---

Product Assets

- [Certifications - EZ Series Luminaries CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_EZS40x](#)
- [Photometry - KIL_EZS40x-A](#)
- [Photometry - KIL_EZS40x-D](#)
- [Photometry - KIL_EZS40x-S](#)
- [Specifications - EZ Series Floodlight Specification Sheet](#)
- [Specifications - EZS405A2-T Specification Sheet French](#)
- [Specifications - EZS405A2T Specification Sheet English](#)



A Hubbell brand