



FXCS-2S3L6G-M - FXCS Series, Seal-XM, AL Dead-End 3-Pos Spring Standard Selector Switch, Return to Ctr, 3/4" Hub, 2NO Contact Rating

By Killark
Catalog # [FXCS-2S3L6G-M](#)

FXCS Series - Seal-XM - Aluminum Dead-End 3-Position Spring
Returned Standard Selector Switch - Return to Center from
Right - Factory Sealed - 3/4" Hub - 2NO Contact Rating

Features

-
-
-
-
-
-
-
-

Application

SEAL-XM Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

General

Action	Momentary Right
Actuator	3 Position Selector Switch
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Back Box Type	FXB
Catalog Number	FXCS-2S3L6G-M
Color	Black
EU RoHS Indicator	Contact Manufacturer
Hub Pattern	Dead-End
Series	Seal-XM
Type	Factory Sealed
UPC	783936002811

Dimensions



Depth	4.84
Hub Size	3/4"

Electrical Ratings

Amperage Rating	10 A
Frequency Rating	50/60 Hz

Certifications And Compliance

CSA File Number	LR11714, 2493125
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
Nema Rating	3

Logistics

Factory Sealed	Factory Sealed
----------------	----------------

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - FXCS Series Factory Sealed Control Stations CSA Certification](#)
- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - FXCS Seal-XM IOM K1390](#)
- [Specifications - SEAL-XM Series Factory Sealed Controls Specification Sheet](#)
- [Specifications - FXCS2S3L6GM Specification Sheet English](#)
- [Specifications - FXCS-2S3L6G-M Specification Sheet French](#)