



GEBT-24 - GEB Outlet Body, T Type, Aluminum- Hub Size (2) 3/4" (1) 1-1/4"

By Killark
Catalog # [GEBT-24](#)

GEB Outlet Body, T Type, Aluminum- Hub Size (2) 3/4" (1) 1-1/4".



*Representative Image

Features

- Suitable for NEMA 4X applications
- Integral mounting lugs
- Green ground screw standard
- External cover thread on body plus smooth integral hub bushing protects conductor insulation when pulling
- Taper threaded hubs provide ground continuity
- External threaded body for additional wiring room
- Includes cover and gasket

General

Application	
Catalog Number	GEBT-24
Color	Gray
	Gris
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Hub Pattern	T
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GE
Type	
UPC	783936114866

Dimensions

Dimensions	6.63 in x 6 in x 4.38 in
Gross Weight with Packaging	3.5
Height	4.38 in
Hub Size	3/4" & 1-1/4"
Length	6.63 in
Width	6 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D
	Class I, Zones 1 & 2, Groups IIC, IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E10514

Product Assets

- [3D Models - GEBT-24 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - GEB Series Outlet Bodies UL Certification](#)
- [Certifications - GEB Series Enclosures CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - GEBT-24 Engineering Drawing](#)
- [Installation Manuals - KIL_GEB Series Outlet Bodies IOM_K1432](#)
- [Sales Drawings - GEBT-24 Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GEBT24-SPEC-EN | REV 6/2024