



GECLT-2 - 3/4" GEC Outlet Body L-Type

By Killark
Catalog # [GECLT-2](#)

3/4" GEC Outlet Body L-Type

Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

General

Catalog Number	GECLT-2
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	L
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GE
UPC	783936210094

Dimensions



*Representative Image

Dimensions	6.25 in x 6 in x 4.25 in
Gross Weight with Packaging	1.84
Height	4.25 in
Hub Size	3/4"
Length	6.25 in
Width	6 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA
UL File Number	E10514

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - GEC Series CSA Certificate of Compliance](#)
- [Certifications - GE Series Outlet Boxes ATEX Certificate](#)
- [Certifications - GEC Series Luminaire Fittings UL Certification](#)
- [Certifications - GE Series Outlet Bodies UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_GEC Series Outlet Bodies IOM_K1457](#)
- [Specifications - GECLT2 Specification Sheet English](#)
- [Specifications - GECLT-2 Specification Sheet French](#)
- [Specifications - GE/GEB Series Outlet Bodies Specification Sheet](#)



A Hubbell brand