



# GECTT-2 - 3/4" GEC Outlet Body T-Type

By Killark  
Catalog # [GECTT-2](#)

3/4" GEC Outlet Body T-Type



\*Representative Image

## Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

## General

Catalog Number	GECTT-2
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	T
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GE
UPC	783936210124

## Dimensions

Dimensions	6.375 in x 6 in x 4.25 in
------------	---------------------------

Gross Weight with Packaging	1.81
Height	4.25 in
Hub Size	3/4"
Length	6.375 in
Weight	1.81 lb
Width	6 in

## Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li></ul>
UL File Number	E10514

## Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - GEC Series CSA Certificate of Compliance](#)
- [Certifications - GE Series Outlet Boxes ATEX Certificate](#)
- [Certifications - GEC Series Luminaire Fittings UL Certification](#)
- [Certifications - GE Series Outlet Bodies UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL\\_GEC Series Outlet Bodies IOM\\_K1457](#)
- [Specifications - GE/GE Series Outlet Bodies Specification Sheet](#)
- [Specifications - GECTT2 Specification Sheet English](#)
- [Specifications - GECTT-2 Specification Sheet French](#)



A Hubbell brand