

## GECTT-2M - 3/4" GEJ Outlet Body T-Type, Iron

By Killark

Catalog # **GECTT-2M****3/4" GEJ Outlet Body T-Type, Iron**

\*Representative Image

### Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

### General

Catalog Number	GECTT-2M
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	T
Material	Iron
Series	GE
UPC	783936210919

### Dimensions

Dimensions	6.375 in x 6 in x 4.25 in
------------	---------------------------

Gross Weight with Packaging	3.51
Height	4.25 in
Hub Size	3/4"
Length	6.375 in
Weight	3.51 lb
Width	6 in

### Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li></ul>
UL File Number	E10514

### Product Assets

Catalogs - Killark Catalog
Certifications - GEC Series CSA Certificate of Compliance
Certifications - GE Series Outlet Boxes ATEX Certificate
Certifications - GEC Series Luminaire Fittings UL Certification
Certifications - GE Series Outlet Bodies UL Certification
Customer Notices - Prop 65 Notice
Installation Manuals - KIL_GEC Series Outlet Bodies IOM_K1457
Specifications - GECTT2M Specification Sheet English
Specifications - GE/GEB Series Outlet Bodies Specification Sheet
Specifications - GECTT-2M Specification Sheet French