

By Killark

Catalog # [GECXT-2M](#)

¾" GEC Outlet Body X Type, Iron



Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

Application

Conduit boxes installed in conduit systems within hazardous areas to: protect conductors in threaded rigid conduit, act as pull and splice boxes, interconnect lengths of conduit, change conduit direction, and provide access to conductors for maintenance and future system changes.

Specifications

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D; Class I, Zones 1 & 2, Groups IIB, IIA
---------------------	--

EU RoHS Indicator

UL File Number

CSA File Number

Contact Manufacturer

E10514

LR11716

Configuration

Hub Pattern	X
-------------	---

Dimensions

Gross Weight with Packaging	3.56
Hub Size	3/4"
Width	6.125 in
Height	4.375 in
Length	6.375 in
Dimensions	6.375 in x 6.125 in x 4.375 in

General

Type	Outlet Body With Cover
Material	Iron
UPC	783936211015
Color	Gray

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand