



By Killark
Catalog # [GEMCA-1](#)

1/2" GEM Outlet Body CA Type

Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

Application

Conduit boxes installed in conduit systems within hazardous areas to: protect conductors in threaded rigid conduit, act as pull and splice boxes, interconnect lengths of conduit, change conduit direction, and provide access to conductors for maintenance and future system changes.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D;Class I, Zones 1 & 2, Groups IIB, IIA



UL File Number E10514

Configuration

Hub Pattern CA

Dimensions

Hub Size	1/2"
Length	11 in
Gross Weight with Packaging	0.83
Width	7 in
Height	3.75 in
Dimensions	11 in x 7 in x 3.75 in

General

Color	Gray
Type	Outlet Body With Cover
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936211220

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)