

GEMLB-1 - 1/2" GEM Outlet Body LB Type

By Killark

Catalog # [GEMLB-1](#)

1/2" GEM Outlet Body LB Type



*Representative Image

Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

General

Catalog Number	GEMLB-1
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	LB
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GE
UPC	783936210223

Dimensions

Dimensions	11 in x 7 in x 3.75 in
Gross Weight with Packaging	0.79
Height	3.75 in

Hub Size

1/2"

Length

11 in

Weight

0.79 lb

Width

7 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA
UL File Number	E10514

Logistics

Carton Quantity	5
-----------------	---

Product Assets

3D Models - GEMLB-1 3D Model
Catalogs - Killark Catalog
Certifications - GE Series Outlet Boxes ATEX Certificate
Certifications - GE Series Outlet Bodies UL Certification
Customer Notices - Prop 65 Notice
Engineering Drawing - GEMLB-1 Engineering Drawing
Installation Manuals - KIL_GE Series Outlet Bodies IOM_K1431
Sales Drawings - GEMLB-1 Sales Drawing
Specifications - GE/GEB Series Outlet Bodies Specification Sheet
Specifications - GEMLB-1 Specification Sheet French
Specifications - GEMLB1 Specification Sheet English