



GEMTA-2 - 3/4" GEM Outlet Body TA Type

By Killark
Catalog # [GEMTA-2](#)

3/4" GEM Outlet Body TA Type

Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

General

Catalog Number	GEMTA-2
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Hub Pattern	TA
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	GE
UPC	783936211343

Dimensions

Dimensions	11 in x 7 in x 3.75 in
Gross Weight with Packaging	0.8



*Representative Image

Height	3.75 in
Hub Size	3/4"
Length	11 in
Width	7 in

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA
UL File Number	E10514

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [3D Models - GEMTA-2 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - GE Series Outlet Boxes ATEX Certificate](#)
- [Certifications - GE Series Outlet Bodies UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - GEMTA-2 Engineering Drawing](#)
- [Installation Manuals - KIL_GE Series Outlet Bodies IOM_K1431](#)
- [Sales Drawings - GEMTA-2 Sales Drawing](#)
- [Specifications - GEMTA-2 Specification Sheet French](#)
- [Specifications - GE/GE Series Outlet Bodies Specification Sheet](#)
- [Specifications - GEMTA2 Specification Sheet English](#)



A Hubbell brand