



G Series - Push Button Lockout - For Use With Operator Types GO1/GO21/GOL1

By Killark
Catalog # [GO-10502](#)

G Series - Push Button Lockout - For Use With Operator Types
GO1/GO21/GOL1.



*Representative Image

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

For use with G Series custom control panel operators.

General

Action	Lockout
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
EU RoHS Indicator	Contact Manufacturer
Series	GO
Type	<ul style="list-style-type: none"> • Push Button Lockout • Push Button Lockout
UPC	783936221281

Dimensions

Dimensions	1.25 in x 1.25 in x 0.625 in
Gross Weight with Packaging	0.1
Height	0.625 in
Length	1.25 in
Width	1.25 in

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.