



# G Series - G Rotary Or Motor Shaft Operator - 3/8 In Shaft Diameter - Male-Female

By Killark  
Catalog # GO18

G Series - G Rotary Or Motor Shaft Operator - 3/8 In Shaft Diameter - Male-Female.



\*Representative Image

## Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

## General

Action	Rotary
Actuator	Motor Shaft Operator
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Application	
Catalog Number	GO18
EU RoHS Indicator	Contact Manufacturer
Series	GO
Type	
UPC	783936220062

## Dimensions

Dimensions	6.31 in x 2.25 in x 1.25 in
Gross Weight with Packaging	0.5
Height	1.25 in
Length	6.31 in
Width	2.25 in

## Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------

## Certifications And Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2

## Product Assets

[Certifications - GO Series Operators CSA Certificate of Compliance](#)  
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-GO18-SPEC-EN | REV 6/2024