



# G Series - G Rotary Or Motor Shaft Operator - 3/8 In Shaft Diameter - Male-Male

By Killark  
Catalog # [GO19](#)

G Series - G Rotary Or Motor Shaft Operator - 3/8 In Shaft Diameter -Male-Male.



\*Representative Image

## Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

## Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

## General

Action	Rotary
Actuator	Motor Shaft Operator
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
EU RoHS Indicator	Contact Manufacturer
Series	GO
Type	<ul style="list-style-type: none"> <li>• Specialty</li> <li>• Specialty</li> </ul>
UPC	783936220086

## Dimensions

Dimensions	6.5 in x 2.125 in x 1.687 in
Gross Weight with Packaging	0.68
Height	1.687 in
Length	6.5 in
Width	2.125 in

## Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------

## Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Divisions 1 &amp; 2, Groups C, D</li> <li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
---------------------	--

## Product Assets

[Certifications - GO Series Operators CSA Certificate of Compliance](#)  
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.